




Caltech

MERCURY THERMOMETER EXCHANGE PROGRAM

The Caltech EH&S Office, in collaboration with the Caltech Sustainability Program, are proud to present a great opportunity for the Caltech laboratory community, where you and your team can exchange your intact mercury thermometers for environmentally friendly non-mercury thermometers for **FREE!!**

Benefits of the Program:

- Reduce labwork downtime from mercury spills
- Improve health and safety in your lab as well as being able to contribute to protecting the environment
- Exchange up to 5 thermometers FOR FREE!!



To start, please fill out an online request at

http://safety.caltech.edu/manuals/Mercury_Thermometer_Exchange

with your information, and choose from the following options:

FOR DIRECT DELIVERY: Indicate the number and model of the approved thermometers you wish to select for the exchange.

FOR PICKUP AT VWR STOCKROOM: We will provide you with a voucher for redemption when we pick up your approved mercury thermometers.

Supplies are limited, so hurry to take advantage of this great offer!

LIST OF APPROVED THERMOMETERS IN THE EXCHANGE PROGRAM

Model: 89095-564 VWR THERMOMETER -20/110C Length: 305 mm General Purpose. Red Spirit Filled Partial Immersion Range: -20 to 110C	Model: 89095-642 VWR THERMOMETER DBLSF -20/150C Length: 305 mm General Purpose. Blue Spirit Filled, Teflon Coated Partial Immersion Range: -20 to 150C
Model: 89095-598 VWR THERMOMETER -20/110C Length: 305 mm General Purpose. Blue Spirit Filled Partial Immersion Range: -20 to 110C	Model: 89095-572 VWR THERMOMETER -20 TO 110C Length: 305 mm General Purpose. Red Spirit Filled Total Immersion Range: -20 to 110C
Model: 89095-604 VWR THERMOMETER -10/260C Length: 355 mm General Purpose. Blue Spirit Filled Partial Immersion Range: -10 to 260C	Model: 89095-654 VWR THERMOMETER DBLSF -10/110C Length: 200 mm General Purpose. Blue Spirit Filled, Teflon Coated Total Immersion Range: -10 to 110C
Model: 89095-640 VWR THERMOMETER DBLSF -20/110C Length: 305 mm General Purpose. Blue Spirit Filled, Teflon Coated Partial Immersion Range: -20 to 110C	NOTE: Teflon coated thermometers are shatter resistant.